




APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	10/04/11	
A		UPDATED BOARDLOCK DIM.	2/10/17	HR/CT

D

D



## SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Copper underplate on tails.

Electrical:

Voltage rating: 250V AC, DC

Current rating: 5A AC, DC

Contact resistance: 10 mohms max


Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature range:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



PACKAGED ON TAPE &amp; REEL

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED  
 INCHES HOLES  
 $.X \pm .10$   $\emptyset X \pm .10$   
 $.XX \pm .020$   $\emptyset XX \pm .015$   
 $.XXX \pm .015$   $\emptyset XXX \pm .010$

APPROVALS		DATE
DRAWN	TW	10/04/11
CHECKED	AY	10/04/11
APPROVED		
SIZE	PART NO.	REV.
X	DML-XX-A-V-T-SMT-BL-PP-T/R	A
REF: S00123T	SCALE: NTS	SHEET 1 OF 1



**ADAM  
TECH**  
INTERCONNECTS

909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

.118 [3.00] DUAL ROW HEADER, VERTICAL  
 SMT TYPE, WITH CAP