



+ CONNECTORS

IN-SERIES ADAPTERS



✓ Active

TE CONNECTIVITY (TE)
2780 0000 00
Subminiature Coax | [SAM](#) , [SMA](#)

1056333-1
TE Internal Number: 1056333-1
Alias ID: 2780-0000-00

[EU RoHS Compliant with Exemptions](#)
[EU ELV Compliant with Exemptions](#)

RF Connector Type SMA
50 Ohm Yes
75 Ohm No
Body Style Straight
Center Contact Material Beryllium Copper

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

OSM 27GHz HIGH FREQUENCY JACK TO JACK ADAPTER
PDF [\(TIFF AVAILABLE\)](#)
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

SMA In-Series Adapters

PDF

English

Qualification Test Report

SMA In-Line Adapters

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- RF Connector Type SMA
- Dielectric Material TFE Fluorocarbon
- Product Type Adapter
- Isolated Ground No
- Retractable Collar Without

Configuration Features

- Snap-Lock Without

Electrical Characteristics

- 50 Ohm Yes
- 75 Ohm No
- Impedance (Ω) 50

Signal Characteristics

- Frequency (GHz) 27

Body Features

- Body Plating Material Gold
- Body Style Straight
- Body Material Stainless Steel
- Body Insulation Without

Contact Features

Center Contact Material Beryllium Copper
Center Contact Plating Material Gold
Center Contact With

Mechanical Attachment

Safety Wire Holes Without

Dimensions

Length 12.7 mm [.5 in]

Packaging Features

Packaging Method Package

Other

Comment Captured Center Contact, High frequency.

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF