

Universal Reversible USB 2.0 Extension Cable (Reversible A to A M/F), Black, 10 ft. (3.05 m)

MODEL NUMBER: UR024-010



Universal USB-A cable with reversible male connector extends a USB cable run by 10 feet.

Features

USB-A Extension Cable Lengthens Your Connection up to 10-ft. (3.05 m)

Extend your USB-A cable run up to 10 feet with this USB 2.0 cable (M/F). It supports data transfer rates up to 480 Mbps, making it ideal for your multimedia application, such as digital signage. The cable is backward compatible with earlier USB generations, including USB 1.1.

Reversible Male Plug Connects in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible male connector plugs into a USB-A port in either direction for an instant connection every time.

Premium Construction Results in Premium Signal Quality

Molded nickel-plated connectors with gold-plated contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. Foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable move freely without cracking or breaking loose from the connector.

Highlights

- Supports USB 2.0 speeds up to 480 Mbps to ensure reliable data transfers
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief helps cable move freely without stress or cracking
- Reversible male plug connects in either direction for immediate no-fuss use

Package Includes

- UR024-010 Universal USB-A Extension Cable (M/F), Black, 10-ft. (3.05 m)

Specifications

OVERVIEW	
UPC Code	037332179609
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	USB A (FEMALE)
Connector Style	Straight



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.