

JOIN OUR NEWSLETTER



SEARCH



BROWSE BY
**PRODUCT
CATEGORY**



BROWSE BY
**DEVICE
MANUFACTURER**



ADVANCED
**INDUSTRIAL
SEARCH**

[Home](#) / [UL40AAVP](#)

PART#: UL40AAVP

Chemistry:	Alkaline-Manganese Dioxide (Zn/MnO ₂)
Voltage:	1.5
Capacity:	2100mAh
Measurements:	5.9" x 2.5" x 2.3" 149.86mm x 63.50mm x 58.42mm

[Find a Distributor](#)



hover to zoom; click to enlarge

40 Pack AA, Bulk, Color Packaged Box

SPECIFICATIONS

Shipping Weight (oz)	35.1000
Manufacturer	Ultralast
Warranty	6
UPC	07609710839
Length	5.9" (149.86mm)
Width	2.5" (63.50mm)
Height / Diameter	2.3" (58.42mm)
Voltage	1.5
mAh	2100
Number of Cells	1
Battery Chemistry	Alkaline-Manganese Dioxide (Zn/MnO ₂)
Rechargeable	Non-Rechargeable
Qty Per Package	40
Weight	35.1 oz

Compatible Batteries and Devices

[Batteries \(5\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way with any of the manufacturers listed in this catalog and the batteries sold in this catalog have not been sponsored or approved by any of such manufacturers. Any trademarks or model numbers listed in this catalog are identified for compatibility or cross-reference purposes only.

RELATED PRODUCTS

THIS ITEM IS
**NO LONGER
AVAILABLE**

Part# [ALK-AA-EVIND](#)

Volts 1.5

Chem Alkaline-Manganese
Dioxide (Zn/MnO₂)

mAh 2200

[Find a Distributor](#)



Part# [ALK-AA-EVEREADY](#)

Volts 1.5

Chem Alkaline-Manganese
Dioxide (Zn/MnO₂)

mAh 2200

[Find a Distributor](#)

