

## Han CGM-M M40x1,5 D.22-32mm



Image is for illustration purposes only. Please refer to product description.

Part number	19 00 000 5098
Specification	Han CGM-M M40x1,5 D.22-32mm
HARTING eCatalogue	<a href="https://b2b.harting.com/19000005098">https://b2b.harting.com/19000005098</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> CGM-M
Type of accessory	Cable gland

### Technical characteristics

Tightening torque	≤15 Nm (depending on the cable and the seal insert used)
Wrench size	50
Limiting temperature	-40 ... +100 °C
Degree of protection acc. to IEC 60529	IP68 IP69 / IPX9K acc. to ISO 20653
Size	M40
Clamping range	22 ... 32 mm
Width across corners	55 mm

### Material properties

Material (cable glands)	Brass
Material (seal)	NBR
Material (clamping ring)	Polyamide (PA)
Surface (accessories)	Nickel plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
California Proposition 65 substances	Nickel
California Proposition 65 substances	Naphthalene

## Specifications and approvals

UL / CSA	UL 514B QCRV.E479780 CSA-C22.2 No. 18.3 QCRV7.E479780
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	170 g
Country of origin	Germany
European customs tariff number	84849000
GTIN	5713140123847
ETIM	EC000441
eCl@ss	27140801 Screwed cable gland (electrical)