



Part Number : [351551200](#)

Product Description : 2.50mm Pitch Wire-to-Board Housing, Positive Lock, Natural, 12 Circuits

Series Number : 35155

Status : Not Recommended For New Design

Product Category : Connector Housings

Documents and Resources

Drawings

[351551200_sd.pdf](#)

[351551200_stp.zip](#)

Specifications

[351550200-100.pdf](#)

[PK-35155-001-001.pdf](#)

[PS-35155-001-001.pdf](#)

[PS-35155-002-001.pdf](#)

[PS-35184-001-001.pdf](#)

[PS-68143-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	35155
Description	2.50mm Pitch Wire-to-Board Housing, Positive Lock, Natural, 12 Circuits
Application	Signal, Wire-to-Wire
Product Name	N/A
UPC	800754835350

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	12
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No

Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1.173/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.50mm Pitch Wire-to-Wire Plug Housings	<u>35184</u>
2.50mm Pitch Vertical Headers	<u>35312</u>

Use with Part(s)

Description	Part Number
SPOX Female Crimp Terminals	<u>5103</u>

This document was generated on Apr 21, 2026