

Specifications

Eaton CPL2-3-50TR-R



Eaton CPL2 inductor, 50 nH, 10 A ISAT, 0.28 mΩ resistance, SMT mounting, Ferrite, 6-pins, Three-phase, 750 qty.

Photo is representative



General specifications

PRODUCT NAME	Eaton CPL2 inductor
CATALOG NUMBER	CPL2-3-50TR-R
UPC	051712234771
PRODUCT LENGTH/DEPTH	35 mm
PRODUCT HEIGHT	5 mm
PRODUCT WIDTH	11 mm
PRODUCT WEIGHT	8.56 g
COMPLIANCES	RoHS Compliant
PRODUCT TYPE	Inductor

Product specifications

TYPE	Inductor
MOUNTING	SMT
PHASE	Three-phase
ISAT	10 A
PACKAGE QUANTITY	750
MATERIAL	Ferrite
FREQUENCY RATING	Up to 2 MHz
CONTACT CONFIGURATION	Six-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	0.28 mΩ
INDUCTANCE	50 nH
SERIES	CPL2

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton CPL2 mutli phase power indcutors data sheet](#)

[Eaton Specification Sheet - CPL2-3-50TR-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

