

Specification Sheet

Part Number: 156-00553



Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.

2-Piece Cable Tie with Edge Clip, 8.0" Long, EC21, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg

|                     |                                                                                                                                                                                                                                                                                                                                            |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 156-00553                                                                                                                                                                                                                                                                                                                                  |
| Type                | T50REC21                                                                                                                                                                                                                                                                                                                                   |
| Color               | Black (BK)                                                                                                                                                                                                                                                                                                                                 |
| Quantity Per        | pack                                                                                                                                                                                                                                                                                                                                       |
| Product Description | HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. |
| Short Description   | 2-Piece Cable Tie with Edge Clip, 8.0" Long, EC21, 1 - 3 mm Panel, 50lb, PA66HS/PA66HIRHSUV, Black, 500/pkg                                                                                                                                                                                                                                |
| Global Part Name    | T50REC21-PA66HS/PA66HIRHS-BK                                                                                                                                                                                                                                                                                                               |

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 50              |
| Minimum Tensile Strength (Metric)   | 225             |
| Length L (Imperial)                 | 8.0             |
| Length L (Metric)                   | 202.0           |
| Fixation Method                     | Edge Clip       |
| Identification Plate Position       | none            |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.18            |
| Width W (Metric)                    | 4.6             |
| Bundle Diameter Min (Imperial)      | 0.04            |
| Bundle Diameter Min (Metric)        | 1.0             |
| Bundle Diameter Max (Imperial)      | 1.77            |
| Bundle Diameter Max (Metric)        | 45.0            |
| Thickness T (Imperial)              | 0.05            |
| Height H (Imperial)                 | 0.05            |
| Height H (Metric)                   | 1.2             |

|                                |                                                                                                            |
|--------------------------------|------------------------------------------------------------------------------------------------------------|
| Panel Thickness Min (Imperial) | 0.04                                                                                                       |
| Panel Thickness Max (Imperial) | 0.12                                                                                                       |
| Panel Thickness Min (Metric)   | 1.0                                                                                                        |
| Panel Thickness Max (Metric)   | 3.0                                                                                                        |
| Material                       | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)<br>Polyamide 6.6 heat stabilized (PA66HS) |
| Foot Part Material             | PA66HIRHSUV                                                                                                |
| Material Shortcut              | PA66HIRHS PA66HS                                                                                           |
| Material Cable Tie             | Polyamide 6.6 heat stabilized (PA66HS)                                                                     |
| UV Resistant (Yes/No)          | No                                                                                                         |
| Use Conditions                 | For Indoor and Outdoor Use                                                                                 |
| Operating Temperature          | -40°F to +221°F (-40°C to +105°C)                                                                          |
| Reach Compliant (Article 33)   | Yes                                                                                                        |
| ROHS Compliant                 | Yes                                                                                                        |
| Package Quantity (Imperial)    | 500                                                                                                        |

|                           |            |
|---------------------------|------------|
| Package Quantity (Metric) | 500        |
| Customs Number            | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224  
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.  
[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)