557-246
Elliptical Micro Band Backshell

- Solid EMI Backshell, .25" Flange
- Micro Band Shield Termination
- Qwik-Ty Strain Relief



557-246


This accessory fits D-Subminiature M24308 connectors.
Not compatible with Series 28 HiPer-D

One piece, elliptical Micro band, .25 (6.4) flange. 557-246 aluminum backshell fits M24308 D-Subminiature connectors. Terminate cable braid to backshell with .12 wide (3.0) Micro band. Optional slot for routing individual pigtail shields. Optional Qwik-Ty strain relief arm. Aluminum with stainless steel screws and clips.

TABLE 1
SCREWLOCK OPTIONS


No Designator

4-40 Socket Head Male Screwlocks With Clips




P

4-40 Female Screwlocks (fixed, non-rotating)



E

4-40 Extended Length Slotted Male Screwlocks With Clips



PART NUMBER

	Sample PN→	557T246	M	3		08	S	T	K

Base P/N
557T246 Top Entry

Finish

TZ	Tin-Zinc
MN	Mega-Nickel
JF	Cadmium, Yel. Chromate
M	Electroless Nickel
NF	Olive Drab Cadmium
MT	Nickel-PTFE
ZR	Black Zinc-Nickel


Shell Size
1 2 3 4 5 6

Screwlocks *(Table 1)*

Omit	Socket Head Screwlocks
E	Extended Slotted Male Screwlock
P	Female Screwlocks *(fixed)*


Entry Size

Entry Size	F	Shell Size
04	.500 (12.7)	1-6
05	.625 (15.9)	1-6
06	.750 (19.1)	2-6
07	.875 (22.2)	2-6
08	1.000 (25.4)	2-6
09	1.125 (28.6)	3-6
10	1.250 (31.8)	3-6
11	1.375 (34.9)	3-6
12	1.500 (38.1)	3-6
13	1.625 (41.3)	4-6
14	1.750 (44.5)	4-6
15	1.875 (47.6)	4-6
16	2.000 (50.8)	4-6



Slot

Omit	No Slot
S	Slot *(in banding area)*



Qwik-Ty

Omit	No Qwik-Ty Strain Relief Arm
T	Qwik-Ty Arm Included



Band

Omit	No Band
K	Micro Band Included
J	Micro Slim Band Included
L	Micro-Max Band Included

© 2024 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • Rectangular Accessories

Dimensions in Inches (millimeters) are subject to change without notice.

Downloaded from Arrow.com.