



Part Number : [732511900](#)

Product Description : SMA Jack, Straight, Bulkhead, Solder, Brass Body, Gold (Au) Plated, for RG-405 (.086" Semi-Rigid) Cable, 50 Ohms

Series Number : 73251

Status : Active

Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

[732511900 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	SMA Jack, Straight, Bulkhead, Solder, Brass Body, Gold (Au) Plated, for RG-405 (.086" Semi-Rigid) Cable, 50 Ohms
Application	RF
Product Name	SMA
Style	Cable
Type	Subminiature
UPC	756054232828

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Jack
Keying to Mating Part	N/A
Net Weight	3.794/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead

PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-405, .086" Semi-Rigid Coaxial

This document was generated on Jan 01, 2026