



Part Number : [190980018](#)

Product Description : Krimptite Snap Spade Terminal, for 22-18 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length, Carton

Series Number : 19098

Status : Active

Product Category : Ring and Spade Terminals

Engineering Part Number : AA-1704-06



Documents and Resources

Drawings

[190980018 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19098
Description	Krimptite Snap Spade Terminal, for 22-18 AWG Wire, Stud Size 5-6 (M3-3.5), 14.86mm Length, Carton
Keyword	Spade Terminal, Spade Terminals
Product Name	Krimptite
Style	Spade Snap
Type	Spade Connector, Metric Spade Connector
UPC	800755081374

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.417/g
Packaging Type	Carton

Stud Size	5-6 (M3-3.5)
Wire Size (AWG)	18, 20, 22
Wire Size mm ²	0.35-0.80

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm ² - 0.5mm ²	<u>640030100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

This document was generated on Apr 14, 2026