



Image coming soon

Part Number : [1301180028](#)
Product Description : Box Track, Festoon Tow Car - 5414
Series Number : 130118
Status : Active
Product Category : Festoons
Engineering Part Number : 54143

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Festoons
Series	130118
Description	Box Track, Festoon Tow Car - 5414
Component Type	Car - Lead
Product Name	Aero-Motive
Type	Box Track
UPC	78678863201

Physical

Cable Height - Maximum	19.05mm (.750")
Cable Width - Maximum	98.00mm (3.858")
Combined Cable Weight-Max./Car	24.95kg (55.0 lb)
Depth	89.92mm (3.540")
Duty	Standard - 25kg per Car
Height	144.78mm (5.700")
Length	250.0m (820.0')
Material - Coating	Zinc
Material - Metal	Galvanized Steel
Net Weight	226.790/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	156.46mm (6.160")
Thread Size	N/A
Wire/Cable Type	Flat