
ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	NOTES
1	TLY-13	NEMA 5-15P	1	black overmold
2	TLY-18	C13	1	black overmold
3	30-00248	Wire, 3C, 18 AWG, UL SJT, 300V, 105°C, 7.75 mm, VW-1, PVC	1	



Revision	Date	Description	Prepared by:	Notes: Rated for 10 A at 125 Vac		20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com			
A	8/27/2014	Initial release	2014.08.28 11:17:57 -07'00' Verified by: JM 2014.08.29 14:35:38 -07'00'	RoHS compliant Function test: no open, no rever short circuit, no INT	sed polarity, no				
			DIMENSIONS ARE IN MILLIMETERS TOLERANCES: X: ± 0.5 mm X.X: ± 0.3 mm	Description: Ac cord, 3000 mm, U.S, NEMA 5-15P plug, TLY-13 to C13, TLY-18, 18 AWG, SJT wire, 30-00248		SIZE Part number A 11-00079			
		X.XX: ± 0.5 mm		2		SCALE: 1:2		WEIGHT:	SHEET 1 OF 1