

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191640065

Status:

Active

Overview:


Perma-Seal Terminals

Description:

Perma-Seal Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 10 (M5)

Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19164
Crimp Quality Equipment	Yes
Overview	Perma-Seal Terminals
Product Name	Perma-Seal
Type	Ring
UPC	800753113497
Physical	
Barrel Type	Closed
Insulation	NiAc
Material - Plating Mating	Tin
Net Weight	2.670/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	10 (M5)
Wire Insulation Diameter	7.87mm
Wire Size AWG	10, 12
Wire Size mm²	3.09-5.01
Material Info	
Engineering Number	SC-230-10
Reference - Drawing Numbers	
Product Specification	PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19164-041-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19164 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Industrial Terminals, 10-22 AWG (see ATS)	640017400
Power Crimp Tool Head for Terminals 10-22 AWG Wire	640057400
ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160041

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION