Part Number : 734205861
Series Number : 73420
Status : Active - Proprietary
Product Category : RF / Coaxial Connectors



Drawings

734205861_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active - Proprietary
Category	RF / Coaxial Connectors
Series	73420
Description	SMP-MAX EVO Jack-to-SMP-MAX EVO Jack Adapter, 12.15mm Length, Tri-Metal Plated Body, Machined Center Contact, Tray, 50 Ohms
Application	Telecommunications/Networking, RF
Product Name	SMP-MAX Evolution
Style	Adapter, Within-Series Adapter
Type	Subminiature
UPC	191130522606

Electrical

Frequency	10 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 330 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack/Jack
Keying to Mating Part	N/A
Net Weight	0.323/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.