



Pushing Performance
Since 1945

ICC20_H_BS_ST_CG_9-13_EMC



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 0029
Specification	ICC20_H_BS_ST_CG_9-13_EMC
HARTING eCatalogue	https://harting.com/97000000029

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight EMC version

Version

Size	20
------	----

Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	9 ... 13 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE
Colour (seal)	Red
RoHS	compliant with exemption



Pushing Performance
Since 1945

Material properties

RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	0.103 kg
Country of origin	India
European customs tariff number	85389099
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405