



| | | | | | | | | | | | | | |
|---|----------------|------------|-------------------|-------|-----------|------|-------------------------------|--------|-----------|----|--|--|----------------------------|
| A | 09 65 366 3811 | M3 | 1 | | | | | | | | <p>All Dim. in mm Orig. Size DIN A 4</p> | D-Sub, High temperature, male, standard, 25 poles with solder pins 2,9mm, nuts and grounding board lock. | Maßstab/ Scale 1.5:1 |
| | 09 65 366 6811 | M3 | 2 | | | | | Det. | 15-FEB-02 | JB | | | |
| | 09 65 366 7811 | M3 | 3 | | | | | Insp. | | | | | |
| | 09 65 366 3812 | 4-40 UNC | 1 | 31892 | 22/04/04 | JH | | Stand. | | | | | |
| | 09 65 366 6812 | 4-40 UNC | 2 | 29723 | 05-MAR-02 | CV | | | | | | | |
| | 09 65 366 7812 | 4-40 UNC | 3 | 29750 | 15-FEB-02 | JB | | | | | | | |
| | Part number | Nut thread | Performance level | Mod. | Dat. | Name | HARTING EURL F-95972 Paris | | | | TB 0965366x81x Sub. | Blatt/ Page 1 / | |