



Part Number : [1301460106](#)


Product Description : Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L6-15, 250V, Cord Grip Body Size F2, Silicone Husk

Series Number : 130146

Status : Active

Product Category : Wiring Devices

Engineering Part Number : 25W49



Documents and Resources

Drawings

[1301460106 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L6-15, 250V, Cord Grip Body Size F2, Silicone Husk
IP Rating	IP69K
NEMA Configuration	NEMA L6-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Connector
UPC	78678870086

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F2 1/2"
---------------------	---------

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	190.508/g
Poles	2-pole/3-wire
Receptacle Type	Single

This document was generated on Dec 30, 2025