

Insulator:PBT+G.F UL94V-O BLACK
Contact:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL

Holddown:Brass,100u" TIN OVER 50u" NICKEL


Sheel:Cold Roller Steel,Ni Plated



Rivetlock:Brass,Nickel Plated

LOT NUMBER "XXXX"

└───┬───┘
└───┴───┘

Stands For Calendar Year
Stands For Week Number



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 11MAR2017 CHK DANIEL GORENC 11MAR2017 APVD DANIEL GORENC 11MAR2017		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± ± -		NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 26P - -	
MATERIAL -		FINISH -		WEIGHT SIZE CAGE CODE DRAWING NO A2 00779 C-2311768	
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 of 1
				REV F	