
HellermannTyton

Technical data sheet

Article number:
161-46100 SBPEMC4



Product Group	PE Metal Detectable Spiral Binding
Product Family	SBPEMC
Material	Polyethylene (PE), Stainless Steel (SS)
Colour	Blue (BU)

Bundle Ø max.	20 mm
Bundle Ø min.	5 mm
Flammability	UL 94 HB
Nominal Ø	4 mm
Operating Temperature	-60 °C to +80 °C, intermittent +120 °C
Package Content	30 m
Package Content packed in	carton
Pitch (P)	7.8 mm
Wall (WT)	1.0 mm

HF ✓ RoHS ✓

created on 22. May 2026, 4:25 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.