

Han 3EMC-HTE-M25 w. glued seal



Image is for illustration purposes only. Please refer to product description.

Part number	19 62 003 1447
Specification	Han 3EMC-HTE-M25 w. glued seal
HARTING eCatalogue	https://harting.com/19620031447

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] EMC
Type of hood/housing	Hood
Description of hood/housing	for Han-Brid [®] With glued seal

Version

Size	3 A
Version	Top entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Single locking lever
Field of application	Hoods/Housings for higher EMC requirements
Pack contents	Please order seal screw separately.

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP44 IP65 With seal screw IP67 With seal screw
Type rating acc. to UL 50 / UL 50E	12



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

Commercial data

Packaging size	10
Net weight	77.75 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140171411
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466