

BT3S-M69

Dome-Top® barb ty cable tie, standard cross section, 12.0 (305mm) length, flame retardant nylon 6.6, natural (ivory).

Specs | Packaging Details | Tools | Documents

Add to Favorites Add to BOM

Material	Nylon 6.6
Application	General
Color	Ivory
Cross Section	Standard
Locking Style	Locking
Continuous Use Temperature Range	-76° (-60°) - 212° (100°)
Plenum-Rated	No
Tool	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STS2, STH2
Length In (mm)	12.00 (305.0)
Thickness In (mm)	0.05 (1.3)
Bundle Diameter Range In. (mm)	0.06 (1.5) - 3.00 (76.0)
CE Compliant	Yes
CSA Certified	Yes
Mil. Std. Part Number	NA
UL 62275 Compliant (Type 2, 21)	No
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	No
Environment	Indoor
Installation Temperature	-4°F (-20°C) - 32°F (0°C)
Max. Bundle Diameter (In.)	3.00
Max. Bundle Diameter (mm)	76.0
Max. Continuous Use Temperature	212°F (100°C)
Min. Bundle Diameter (In.)	0.06
Min. Bundle Diameter (mm)	1.5
Min. Loop Tensile Strength (Lbs.)	50.00
Min. Loop Tensile Strength (N)	222
Operating Temperature	-76°F (-60°C) - 239°F (115°C)
Thickness (In.)	0.05
Thickness (mm)	1.3
Width In (mm)	0.18 (4.7)
RoHS Compliancy Status	Compliant

Downloaded from Arrow.com.

Min. Order Qty.	1,000

Downloaded from Arrow.com.