
PXV0745/P/07 Datasheet

Product Name // Vitalis Buccaneer Flex Range (7 Contact)

View Product Page





// Product Description:

- PXV0745/P/07 provides a PCF reduction of 7.7 kg CO_2e per 100 units compared to the equivalent Standard Series Buccaneer part number
- Flex Cable Connector
- Water and dustproof to IP68 when mated with compatible connectors
- Plug contacts
- 7 pole
- Screw contacts, supplied fitted
- 7mm-9mm diameter cable acceptance
- Cable Glands for differing cable diameters available separately individually or in packs
- Cable Support accessory 12237/R available separately
- PXV0734 Sealing Cap available separately to maintain IP rating of unmated connectors
- Mates with Standard Vitalis Series (PXV) and Standard Series (PX) Buccaneer Inline, Panel Mount and Flange Mount Connectors

// General Information:

Product Display Title:	Vitalis Buccaneer Flex Range (7 Contact)
Product Family:	Circular Power Connector
Product Series:	Standard Vitalis Buccaneer
Approvals:	UL, VDE
Body Colour:	Black
Body Material:	Polyamide (PA)- Glass Filled
Body Material Type:	Plastic Body
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	5A
Diameter Over Coupling Ring Mm:	38.1mm
Flamability Rating:	UL94HB
Function:	Flex Cable Connector
Insert Colour:	Black Insert And Gland Nut
Ip Rating:	IP68, IP69K
Max Cable Entry Size:	9mm
Min Cable Entry Size:	7mm
Max Contact Accomodation Awg:	16AWG
Min Contact Accomodation Awg:	17AWG
Max Contact Accomodation Mm2:	1.5mm2
Min Contact Accomodation Mm2:	1mm2
Max Operating Temperature:	+70°C
Min Operating Temperature:	-20°C
Number Of Contacts:	7 Contacts
Rohs Compliant:	Yes
Voltage Max:	277V

// Product PDF Links

Standard Vitalis Buccaneer Product...

// Product 3D CAD Model Links

PXV0745/P/073D CAD Model

Have a question or project enquiry you'd like to talk to us about?

Click Here To Contact Us

Downloaded from Arrow.com.