Specifications



Photo is representative





Eaton KU12

Eaton Bussmann KU series panel mount terminal block connector, 600 V, 60 A, Double row, Standard, 12-pole, 10-32 TPI Screw, Black, Nickel-plated brass terminal

General specifications

PRODUCT NAME	Eaton Bussmann KU series panel mount terminal block connector
CATALOG NUMBER	KU12
UPC	051712588782
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.4 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	Contact Manufacturer
PRODUCT TYPE	Panel mount terminal block connector

Powering Business Worldwide

Downloaded from Arrow.com.

Electrical ratings

AMPERAGE RATING	60A
VOLTAGE RATING	600 V

Physical details

NUMBER OF POLES	Twelve-pole
TYPE	Double row, standard

Resources

CATALOGS	Bussmann series complete full line catalog no. 1007 KU12~TERM BLOCK BLACK NOR
MULTIMEDIA	Bussmann series Fuseology

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.