



**Catalog No. A18-250**

**Description: NON-INS FEM-250 DISC, 22-18 LEN .73**

**UPC No 786210803081**

**Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect**

Non-Insulated Female Disconnect, Length .73 Inches, Width .31 Inches, Tab Size .250x.032, Wire Range #22-#18 AWG, Copper, Tin Plated

**Descriptors**

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

**Specifications**

Material	Brass
Finish	Tin Plated
Color	Metallic
Insulation	None

**Classifications**

Brand Name	Sta-Kon
Standard	UL E66716

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Not isolated
Material	Copper
AWG-range	22-18

**Certification/Standard**

<b>CLASS</b>	<b>File Number</b>	<b>Class</b>	<b>CCN</b>	<b>Certificate Number</b>	<b>Library Number</b>
CSA	4503	622701	N/A	N/A	N/A
CSA	7222	622701	N/A	N/A	N/A
UL	E66716	N/A	N/A	N/A	N/A