


NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS SHIPPED UNASSEMBLED
3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE



ASS'Y P/N	CABLE O.D.
W8880-XPG-P-513	.130-.150 [3.3-3.8]
W8880-XPG-P-516	.160-.180 [4.1-4.6]
W8880-XPG-P-519	.190-.210 [4.8-5.3]
W8880-XPG-P-522	.220-.250 [5.6-6.3]
W8880-XPG-P-526	.250-.270 [6.3-6.9]
W8880-XPG-P-528	.265-.285 [6.7-7.2]

ASSEMBLY P/N	CONTACT QTY
W8880-8PG-P-5XX	8
W8880-9PG-P-5XX	9
W8880-10PG-P-5XX	10
W8880-XPG-P-5XX	




GROMMET SIZE
NUMBER OF CONTACTS




SHOWN ASSEMBLED
FOR CUSTOMER REFERENCE ONLY




MATING FACE
W8880-10PG-P-5XX SHOWN




WIRING END
W8880-10PG-P-5XX SHOWN
WITHOUT HARDWARE



WIRING END
W8880-8PG-P-5XX



WIRING END
W8880-9PG-P-5XX



WIRING END
W8880-10PG-P-5XX

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	07-14-20	RELEASED PER PDR 16014-10			
	PNK	03-20-18	PDR 16014			
REV.	INIT.	DATE	DESCRIPTION			
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED. ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16 ▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			ORIG. DRAWN BY: PNK DATE: 03-20-18 CHECKED BY:		CONXALL 601 E. WILDWOOD VILLA PARK, IL 60181	
			APPROVED BY:			TITLE: CABLE-TO-CABLE ASSEMBLY (8-10) #22 PIN CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X
			SCALE NTS	SIZE B	SHEET 1 OF 1	CUSTOMER: STANDARD PRODUCT
			FILE: W8880-XPG-P-5XX	DIRECTORY: SLW	PART NUMBER: W8880-XPG-P-5XX	REV A