

MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

minimatch 11 pos male

MINI-MATCH | IDC , Mini-Match

1-5161500-1

TE Internal Number: 1-5161500-1

EU RoHS Compliant

EU ELV Compliant

Number of Positions 11

Centerline (Pitch) 2.5 mm [.098 in]

Connector & Contact Terminates To Printed Circuit Board

Connector Style Plug

PCB Mounting Orientation Vertical

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

Mini Match Make Connector 3-20 Pos

PDF (TIFF AVAILABLE)

English

CAD Files

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

3D PDF

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Printed Circuit Board

Connector Style Plug

PCB Mounting Orientation Vertical

Connector Type Connector Assembly

Product Type Connector

Wire/Cable Type Discrete Wire

Configuration Features

Number of Positions 11

Number of Rows 1

Body Features

Color Green

Contact Features

Solder Tail Contact Plating Material Tin over Nickel

Contact Base Material Phosphor Bronze

Contact Mating Area Plating Material Tin

Contact Type Tab

Termination Features

Termination Method to PC Board Through Hole

Termination End Plating Material Tin over Nickel

Mechanical Attachment

Mating Connector Lock Without

PCB Mounting Style Through Hole

PCB Mount Retention Without

Mating Alignment Without

Housing Features

Centerline (Pitch) 2.5 mm [.098 in]

Housing Material Thermoplastic

Housing Color Green

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 1500

Packaging Method Box

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
