



Representative Image

Catalog No. ST21/245GR-G

Description: PVC CTD LT CONN W/GR 45D 2-1/2IN G

UPC No 704508034306

Home > Cable Protection Systems > Ocal > Liquid tight connectors

PVC Coated Liquitight Conduit Connector with Grounding Ring, 45 Degree, Pipe Size 2-1/2 Inch/63 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Dark Gray

Descriptors

Category	Liquid tight connectors
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure

Specifications

Material	Steel
Finish	PVC Coated
Color	Dark Gray
NEMA Rating	4X
Environmental Conditions	Hazardous Locations

Classifications

Brand Name	Ocal
Standard	UL, CSA

Dimensions

Size	2-1/2 Inch/63mm
------	-----------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	63 mm
Nominal size in inch	2 1/2 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Steel

ETIM	EC001180 Screw connection for protective metallic hose
Surface protection	Other