




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/5/07	

APPROVED: _____

DATE: _____ TITLE: _____



P.C.B. LAYOUT

SPECIFICATIONS:

Material:

Insulator: Nylon 6T, rated UL 94V-0

Insulator color: Ivory

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Ratings:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.

Recommended soldering temp: 260°C. for 5 sec.



A=.049 [1.25] X NO. OF SPACES
B=.049 [1.25] X NO. OF SPACES +.114 [2.90]
C=.049 [1.25] X NO. OF SPACES +.173 [4.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710



HIROSE DF13-1.25mm WAFER XXP SMT 90°

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				HOLES			
X	± .10	ØX	± .10	X	± .10	ØX	± .10	X	± .10	ØX	± .10
XX	± .020	ØXX	± .015	XX	± .020	ØXX	± .015	XX	± .020	ØXX	± .015
XXX	± .015	ØXXX	± .010	XXX	± .015	ØXXX	± .010	XXX	± .015	ØXXX	± .010
APPROVALS				DATE							
DRAWN	SS			11/5/07							
CHECKED											
APPROVED											
TITLE				SIZE				PART NO.			
				X				125SH-C-XX-TR-SMT-1TR			
REF:				SCALE: NTS				SHEET 1 OF 2			

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
		SEE SHT 1 OF 2 FOR REVISION HISTORY		



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			
INCHES			
HOLES			
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010
APPROVALS		DATE	
TITLE			
HIROSE DF13-1.25mm WAFER XXP SMT 90°			

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

SIZE	PART NO.	REV.
X	125SH-C-XX-TR-SMT-TR	-
REF:	SCALE: NTS	SHEET 2 OF 2