

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 5 Wire 20A 240V IEC309 740cm

PDM3520IEC309-740

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Lead time	Usually Ships within 3 Weeks

Main

Main Input Voltage	230 V
Main Output Voltage	240 V
Input Connection Type	IEC 60309
Provided equipment	Installation guide

Physical

Colour	Grey
Height	12.7 cm
Width	44.4 cm
Depth	40.6 cm
Product weight	5.36 kg

Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	20 A

Output

Max current draw	20 A
Number of power socket outlets	1 IEC 309

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	40.6 cm
Package 1 Length	44.4 cm
Package 1 Weight	5.91 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	Yes