

Sales Outline Drawing
Revision C

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

| | |
|----------------------------------|--|
| Oscillation Frequency (Hz) | 3800 ± 500 |
| Operating Voltage (Vdc) | 3 ~ 28 |
| Rated Voltage (Vdc) | 12 |
| Current Consumption (mA/max) | 12 at Rated Voltage |
| Sound Pressure Level (dB/min) | 85 at 30cm at Rated Voltage |
| Tone/Pulse Rate (Hz0) | Constant |
| Operating Temperature (°C) | -20 ~ +70 |
| Storage Temperature (°C) | -30 ~ +80 |
| Housing | ABS 777D plastic resin (Color: Black) |
| Lead Pins | Tin Plated Brass |
| Weight (Grams) | 3.8 |
| Condition by wave soldering (°C) | 260 ±5 / within 5 sec |
| Condition by hand soldering (°C) | 350 ±20 / within 5 sec |
| Options | For other options contact factory |

Dimensions: (units: mm)

RoHS Compliant

