Pushing Performance
Since 1945

ICC20 Backshell straight (9-13 mm)



Image is for illustration purposes only. Please refer to product description.

Part number	19 59 120 4011
Specification	ICC20 Backshell straight (9-13 mm)
HARTING eCatalogue	https://harting.com/19591204011

Identification

Category	Connectors
Series	HARTING ICC
Type of hood/housing	Backshell
Description of hood/housing	With integrated cable gland Straight

Version

Size	20

Technical characteristics

Tightening torque	12 Nm Cable gland 15 Nm Backshell
Limiting temperature	-40 ... +125 °C
Number of relockings	≥10
Degree of protection acc. to IEC 60529	IP67 IPX9
Clamping range	9 ... 13 mm

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
Material (seal)	TPE
Colour (seal)	Red
RoHS	compliant

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61984 IEC 60664-1
Approvals	CE

Commercial data

Packaging size	1
Net weight	0.099 kg
Country of origin	India
European customs tariff number	85389099
GTIN	5713140400573
eCl@ss	27440224 Shell for circular connectors
UNSPSC 24.0	39121405

HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.