



**Part Number :** [2300314010](#)

**Product Description :** MiniCirc Female-to-MiniCirc Female Wiring Harness, 1000.00mm Length, 4 Circuits, Blue

**Series Number :** 230031

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents and Resources

### Drawings

[2300314010 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	230031
Description	MiniCirc Female-to-MiniCirc Female Wiring Harness, 1000.00mm Length, 4 Circuits, Blue
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MiniCirc-to-MiniCirc
Product Name	MiniCirc
Type	Overmolded Assembly
UPC	198930555490

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V DC

### Physical

Cable Length	1000.00mm
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Blue
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	PBT
Overmolded	Yes
Packaging Type	Bag

Pitch - Mating Interface	N/A
Plating min - Mating	0.075µm
Plating min - Termination	0.075µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	TPU
Wire Size (AWG)	26

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
MiniCirc Socket Connectors	<u>230030</u>

---

This document was generated on Mar 01, 2026