

SWITCH-BASIC

(M) BZ-RQX66
ISSUE I

REPLACES

RELEASE NO.

CHECK

P.S.

T 57

S.C.H.

29. 人


O. M. W.

MICRO SWITCH
A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, MINNESOTA 
FED. MFR. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-RQX66



NOTE -
1-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX. DIA. ON $1.000^{+0.002}$ CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE - FULL
OPERATING FORCE ----- 6-9 1/2 OZ.		CONTACT ARRANGEMENT SINGLE POLE DOUBLE THROW MAINTAINED CONTACT	BREAK DISTANCE .070 MIN.	DO NOT SCALE PRINT
OVERTRAVEL ----- .188 MIN.				
RESET CHARACTERISTICS		UNDERWRITERS LAB. INC. LISTED RATING 15A-125, 250, OR 480 VAC 1/4 HP-125 VAC; 1/2 HP-250 VAC -L67- 1/2 A-125 VDC; 1/4 A-250 VDC 		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
OPERATING FORCE ----- 2-10 OZ.				ONE PLACE (.0) ±.030
OVERTRAVEL ----- .015 MIN.				TWO PLACE (.00) ±.018
				THREE PLACE (.000) ±.008
				ANGLES ±
				WEIGHT

RASTOR