



Copyright FCI.



FCIconnect.com







1 | 2

3 |

4

PRODUCT NUMBER	PITCH
KGxx00x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material

- Item ③ Terminal (Body): Thermoplastic (UL94 V-0)
- Item ④ Male contact pin: Brass, Tin plated

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 15A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec

DIMENSION

Dim A	(N-1)×5.0+2.8
Dim B	N×5.0
Dim C	(N-1)×5.0

N=Number of poles

Poles	Tolerance
2p-6p	±0.15
7p-13p	±0.20
14p-18p	±0.30
19p-24p	±0.40

PART NO.: KG xx 00 x 0 00J0 G

Solid block	0	Color	Black (RAL9005)	RoHS compliant
No. of poles	2		Red (RAL3001/D)	(lead<4%)
02 2 poles	3		Orange(RAL2011/P)	In copper Alloy
03 3 poles	4		Yellow(RAL1018/A)	
...	5		Green(RAL6018/T)	
24 24 poles	6		Blue (RAL5015/A)	
	8		Grey(RAL7035/D)	
	9		White(RAL1102)	
	C		Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family TERMINAL BLOCK			
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	title TERMINAL BLOCK			
					angles	scale	PLUGGABLE SOCKET, VERTICAL			
					X±0.5		dwg no			
					X.X±0.3		sheet 1 of 1			
					X*±1°		size			
					dr	EVIN ZHONG	A4			
					enr	EVIN ZHONG	KGxx00x000J0G			
					chr	HANKE FENG	type			
					appd	SHI JUN	CUSTOMER Drawing			
sheet index	revision	A								
	sheet	1								