

PLG - HSB box shrink tube

PLG-HSB box shrink tube- the shrinking tubing in an handy box is especially interesting for small consumers. With a shrinking ratio is 2:1 the tubing guarantees an effective electrical insulation.



Flame-retardant



UV-resistant



Waterproof

Application range

General purpose, flexible heat shrink tubing for protection, insulation and bundling

Benefits

Convenient amount of heatshrink, for small users

Flexible, rapid shrinkage, non-melting for effective electrical insulation

Stackable boxes for easy storage

Flame-retardant

Product features

UV-resistance is tested according to ASTM 154

Technical Data

Note:	Good chemical resistance Thin walled
Info:	Shrinking ratio: 2:1 Length change during shrinking: maximum $\pm 10\%$
Colour delivered:	Black- UV-resistant Transparent - halogen-free
Material:	Cross-linked polyolefin, Silicone, Cadmium and Lead free
Temperature range:	-55°C to +125°C Shrinking temperature: +110°C

Note

Other colours are available upon request.

Photographs are not to scale and do not represent detailed images of the respective products.

**PLG - HSB box shrink tube**

Part number	Article description	Internal Ø before contraction (mm)	Shrinkage range (mm)	Panel thickness/ shrunk +- 0.1 mm	Contents (m)	PU
Black						
61752220	HSB 46-0	1.2	1,2 - 0,6	0.4	12.0	1
61752230	HSB 63-0	1.6	1,6 - 0,8	0.4	12.0	1
61752240	HSB 93-0	2.4	2,4 - 1,2	0.5	11.5	1
61752250	HSB 125-0	3.2	3,2 - 1,6	0.5	11.5	1
61752260	HSB 187-0	4.7	4,7 - 2,4	0.5	9.5	1
61752270	HSB 250-0	6.4	6,4 - 3,2	0.6	7.5	1
61752280	HSB 375-0	9.5	9,5 - 4,8	0.6	6.5	1
61752290	HSB 500-0	12.7	12,7 - 6,4	0.7	6.0	1
61752300	HSB 750-0	19.1	19,1 - 9,5	0.7	5.0	1
61752310	HSB 1000-0	25.4	25,4 - 12,7	0.8	3.3	1
transparent						
61752830	HSB 46-C	1.2	1,2 - 0,6	0.4	12.0	1
61752840	HSB 63-C	1.6	1,6 - 0,8	0.4	12.0	1
61752850	HSB 93-C	2.4	2,4 - 1,2	0.5	11.5	1
61752860	HSB 125-C	3.2	3,2 - 1,6	0.5	11.5	1
61752870	HSB 187-C	4.7	4,7 - 2,4	0.5	9.5	1
61752880	HSB 250-C	6.4	6,4 - 3,2	0.6	7.5	1
61752890	HSB 375-C	9.5	9,5 - 4,8	0.6	6.5	1
61752900	HSB 500-C	12.7	12,7 - 6,4	0.7	6.0	1
61752910	HSB 750-C	19.1	19,1 - 9,5	0.7	5.0	1
61752920	HSB 1000-C	25.4	25,4 - 12,7	0.8	3.3	1