



Part Number : [1512072204](#)
Product Description : CP-6.5 Receptacle Housing,
Glow-Wire Capable, 6.50mm Pitch, Dual Row, 2
Circuits, Purple
Series Number : 151207
Status : Active
Product Category : Connector Housings

Documents & Resources

Drawings

- [1512072204_sd.pdf](#)
- [1512070001-PK-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [PS-151048-0001-001.pdf](#)
 - [2034380001-PS-000.pdf](#)
 - [2035550001-PS-000.pdf](#)
 - [1512070001-TS-000.pdf](#)
 - [2034380001-TS-000.pdf](#)
 - [2035550001-TS-000.pdf](#)
-

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	151207
Description	CP-6.5 Receptacle Housing, Glow-Wire Capable, 6.50mm Pitch, Dual Row, 2 Circuits, Purple
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Product Name	CP-6.5
UPC	191128438407

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	2
Color - Resin	Purple
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.007/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.50mm
Pitch - Termination Interface	6.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
CP-6.5 Header, 6.50mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Tray Packaging, Glow-Wire Capable, 2 Circuits, Purple	<u>1510481204</u>
CP-6.5 Header, 6.50mm Pitch, Dual Row, Vertical, Polarized, Positive Lock, Tube Packaging, Glow-Wire Capable, 2 Circuits, Purple	<u>1510482204</u>
CP-6.5 Plug Housing, 6.50mm Pitch, Dual Row, 2 Circuits, Purple, Glow-Wire Capable	<u>2034382204</u>

Use with Part(s)

Description	Part Number
CP-6.5 Terminal Position Assurance (TPA) Retainer, 1 Circuit	<u>511430105</u>
CP-6.5 Female Crimp Terminals	<u>50597</u>
CP-6.5 Female Crimp Terminals	<u>50598</u>

This document was generated on Sep 24, 2025