



Part Number : 1301080183

Series Number : 130108

Product Category : Lamps and Lights

Product Description : Watertite Wet Location
40W Fluorescent Hand Lamp with Switch,
Cord Type 16/3 SJTOOW, Cord Length 7.62m
(25.0')

Status : Planned for Obsolescence

Engineering Number : 1940SA

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Planned for Obsolescence
Category	Lamps and Lights
Series	130108

Description	Watertite Wet Location 40W Fluorescent Hand Lamp with Switch, Cord Type 16/3 SJTOOW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Wide-Area Lighting Products
Product Name	Watertite
Type	Wide Area Lamps
UPC	78678830277

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	40W
Lumens	3150
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SJTOOW
Depth	69.85mm (2.750")
Duty	Wet Location
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	PL-L 40/41
Length	825.50mm (32.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Outlet	None

Packaging Type	Carton
----------------	--------

This document was generated on Jul 03, 2024