

Connection Systems Catalog

Search by part# or keyword



FIND BY FEATURE

BROWSE BY CATEGORY

COMPARISON LIST (0)

CUSTOMER SERVICE

REQUEST SAMPLES

SEARCH RESULTS (1)

SEARCH OPTIONS

1 Result(s): [All] - 33105194

☐ Compare



☐ 33105194 Charge Coupler
Connetor Pigtail, Rubber Overmol
d Handle, Cable Length 6.20 m/20.
33 ft

☐ Compare

Charge Coupler Connetor Pigtail, Rubber Overmold Handle, Cable Length 6.20 m/20.33 ft



Part # 33105194

[Question about this product?](#)

ATTRIBUTES

Units: **Metric** English

Attributes

Part #	33105194
Sealable	Mat Sealed
Family	Sleeve / Pin
Product Type	Cable Assembly
Remarks	Charge Coupler: SAE J1772/IEC62196 Type I; Handle: Rubber overmold; Electrical Rating: 16A, 240 VAC; Cable Description: 3 - 2.5mm2 x 1 - 0.75mm2 IEC Cable; Cable Length (m/ft): 6.20 m/20.33 ft; Certifications/Approvals: UL, CE
Series	Charge Coupler
Type	product