

High-Density Fiber Adapter Panel (MMF/SMF), 6 SC Duplex Connectors, Black

MODEL NUMBER: **N492-06D-SC**



Toolless pass-through fiber panel snaps easily into Tripp Lite wall-mount fiber enclosures to complete singlemode or multimode fiber connections.

Description

The N492-06D-SC High-Density Fiber Adapter Panel (MMF/SMF) is designed specifically for use with Tripp Lite's N492-WM2-BK or N492-WM4-BK Wall-Mount Fiber Enclosures. The pass-through panel features six SC duplex connectors that work with both multimode and singlemode applications. It's easy to install—just snap the panel into the enclosure with no tools required. It's made from heavy-duty 1.2 mm cold-rolled steel that will last a lifetime. Dust caps are included to protect unused connectors from debris or damage.

Features

High-Density Fiber Adapter Panel for Pass-Through Applications

- Recommended for multimode or singlemode fiber connections
- Simple snap-in installation with no tools required
- 6 SC duplex connectors
- Heavy-duty 1.2 mm cold-rolled steel construction
- Dust caps protect unused connectors from debris and damage
- Compatible with Tripp Lite N492-WM2-BK or N492-WM4-BK Wall-Mount Fiber Enclosures

Specifications

OVERVIEW	
UPC Code	037332202956

Highlights

- Simple installation with no tools required
- Made from heavy-duty 1.2 mm cold-rolled steel
- Includes dust caps to protect unused connectors
- Works with multimode and singlemode fiber
- Features 6 SC duplex connectors

System Requirements

- Tripp Lite N492-WM2-BK or N492-WM4-BK wall-mount fiber enclosure

Package Includes

- N492-06D-SC High-Density Fiber Adapter Panel (MMF/SMF)
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	3.56 x 13.97 x 5.33
Shipping Dimensions (hwd / in.)	1.40 x 5.50 x 2.10
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
Unit Dimensions (hwd / in.)	1.2 x 5.1 x 1.2
ENVIRONMENTAL	
Operating Temperature Range	-40 to 140 F (-40 to 60 C)
CONNECTIONS	
Ports	6
Side A - Connector 1	SC DUPLEX (FEMALE)
Side B - Connector 1	SC DUPLEX (FEMALE)
FEATURES & SPECIFICATIONS	
Technology	Multimode; Singlemode
CERTIFICATIONS	
Approvals	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>