


6		5	4	3	2	1
PART NUMBER	TITLE		CABLE DESCRIPTION	LENGTH 'L'	CABLE COLOR	
2147631101	MICROFIT 3.0 M-S 75MM 22AWG LEAD BK Sn		1X22AWG DISC SR-PVC BK UL10002	75±3	BLACK	
2147631102	MICROFIT 3.0 M-S 150MM 22AWG LEAD BK Sn		1X22AWG DISC SR-PVC BK UL10002	150±5	BLACK	
2147631103	MICROFIT 3.0 M-S 225MM 22AWG LEAD BK Sn		1X22AWG DISC SR-PVC BK UL10002	225±5	BLACK	
2147631104	MICROFIT 3.0 M-S 300MM 22AWG LEAD BK Sn		1X22AWG DISC SR-PVC BK UL10002	300±5	BLACK	
2147631105	MICROFIT 3.0 M-S 450MM 22AWG LEAD BK Sn		1X22AWG DISC SR-PVC BK UL10002	450±5	BLACK	
2147632101	MICROFIT 3.0 M-S 75MM 22AWG LEAD RD Sn		1X22AWG DISC SR-PVC RD UL10002	75±3	RED	
2147632102	MICROFIT 3.0 M-S 150MM 22AWG LEAD RD Sn		1X22AWG DISC SR-PVC RD UL10002	150±5	RED	
2147632103	MICROFIT 3.0 M-S 225MM 22AWG LEAD RD Sn		1X22AWG DISC SR-PVC RD UL10002	225±5	RED	
2147632104	MICROFIT 3.0 M-S 300MM 22AWG LEAD RD Sn		1X22AWG DISC SR-PVC RD UL10002	300±5	RED	
2147632105	MICROFIT 3.0 M-S 450MM 22AWG LEAD RD Sn		1X22AWG DISC SR-PVC RD UL10002	450±5	RED	



ITEM	PART#	DESCRIPTION	QTY	UOM
A	430310001	MicroFit 3.0 M Crp Term Chn Tin 20-24	1	PC

- Notes:
- Crimping to be done as per Molex standards.
 - The product specification relies on the terminals & wire spec.
 - Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 0.9mm Max.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2020/03/02	A	INITIAL RELEASE	AS20
2020/07/08	A1	TINNING DIA UPDATED	ARAJU

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 641231 DRWN: ARAJU 2020/07/08 CHK'D: RDESAI01 2020/07/10 APPR: RDESAI01 2020/07/10 INITIAL REVISION: DRWN: AS20 2020/02/28 APPR: RDESAI01 2020/05/14			molex					
 = 0		mm		NTS					SEE TABLE					
 = 0		GENERAL TOLERANCES (UNLESS SPECIFIED)												
 = 0		ANGULAR TOL ± °												
 = 0		4 PLACES		±					PRODUCT CUSTOMER DRAWING					
 = 0		3 PLACES		±										
 = 0		2 PLACES		±										
 = 0		1 PLACE		±					DOCUMENT NUMBER		DOC TYPE		DOC PART	REVISION
 = 0		0 PLACES		±					2147631101		PSD		000	A1
 = 0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER				
 = 0						A4-SIZE		214763		SEE TABLE		CUSTOMER		
										SHEET NUMBER				
										1 OF 1				

DOCUMENT STATUS	P1	RELEASE DATE	2020/07/10	09:42:31
-----------------	----	--------------	------------	----------