

Product data sheet

Specifications



32' CABLE EXTENDER 5-WIRE #10 AWG, UL WITH L21-20R/P

PDW32L21-20XC

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	120 V 208 V 3 phases
Input Connection Type	NEMA L21-20P
Number of cables	1
Provided equipment	Installation guide

Physical

Colour	Black
Height	6.4 cm
Width	5.1 cm
Depth	975.4 cm
Net weight	4.68 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Permissible voltage	200...240 V
Max line current	20 A

Output

Max current draw	20 A
------------------	------

Conformance

Product certifications	UL listed
------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	10.2 cm
Package 1 Width	44.5 cm
Package 1 Length	30.5 cm
Package 1 Weight	4.95 kg

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)