
# CT30125C00, Cable Tie, 1.25" Bundle, 30 Lb Tensile, UV Black



By Burndy
Catalog # CT30125C00

Nylon UNIRAP™ Cable Tie - 30 Lb. Tensile Strength, UV Black, Nylon 6/6, 5.84" Long, 100 pack

## Features

- Standard Cable Tie
- Suitable for General Use
- Most sizes are available in Natural or Black

## Specifications

| | |
|---|---|
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Standards - Industry Standards Met | Military Specified (Mil-Spec) |
| Standards - RoHS Compliance Status | CM |
| Certification - cULus | No |
| Certification - UV Rated | Yes |
| Industry Standard(s) | Military Specified (Mil-Spec) |
| UL Listed | No |
| Certification - CSA Approved | No |
| Military Spec Number | MS3367-5-0 |
| Certification - 94V0 Rated | N |

## Dimensions

| | |
|---|---|
| Package Height | 0.000 in |
| Length | 5.84 in |
| Package Weight | 0.000 lb. |
| Dimension - Width mm | 3.6 mm |
| Dimension - Width inch | 0.14 in |
| Package Length | 0.000 in |
| Package Width | 0.000 in |
| Dimension - L Length Overall mm | 146 mm |
| Width | 0.14 in |
| Dimension - Length Overall inch | 5.75 in |
| Dimension - Bundle Diameter Max inch | 1.25 in |

## Force Related

| | |
|---|---|
| Rating - Minimum Tensile Strength lbs | 30 |

## General

| | |
|---|---|
| Color | UV Black (Mil. Spec.) |
| Trade Name | UNIRAP™ |
| Series | UNIRAP™ Series |
| Tool Type | Intermediate |
| UPC | 781810332283 |
| Material | Nylon 6/6 |
| Military Specification | MS3367 |
| UPC 14 Digit GTIN | 00781810332283 |

## Logistics

| | |
|---|---|
| Minimum Pack Quantity | 100 |
| Carton Quantity | 1000 |
| Packaging Type | Bag |

## Operational

| | |
|---|---|
| Operating Temperature Celcius Max | 85 °C |
| Operating Temperature Celcius Min | -40 °C |

## Product Assets

Catalog [English]



© 2026 Hubbell Incorporated. All rights reserved


Downloaded from Arrow.com.