



TP144, Vinyl Ring Terminal For 16 - 14 AWG

By Burndy
Catalog # [TP144](#)

Vinyl Ring Terminal For 16 - 14 AWG



Features

- Expanded insulation support accepts standard and large wire diameters providing lower inventory requirements and greater flexibility
- Funnel entry for easy wire insertion
- Manufactured of pure electrolytic copper to provide maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Deep V groove serrations in the inner barrel provides added holding strength and better conductivity

Application

For Commercial And Light Duty Industrial Control And Power Circuit Applications

Specifications

Buy American Compliant	Yes
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Industry Standard(s)	UL467
Buy America(n) Qualified	- Buy America Compliant (All status valid till December 2025) - Buy American Act Compliant (All status valid till December 2025) - BABA Compliant (All status valid till December 2025)
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor Size	16 - 14 AWG
Conductor Type	- CU C Solid-Size - CU C Str-Size
Conductor Range	#16 AWG to #14 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Dimension - L Length Overall mm	20 mm
Dimension - Pad Width inch	0.21 in
Dimension - Hole Size fraction	3/25
Dimension - Hole Size inch	0.12 in
Dimension - Strip Length inch	13/64 in
Dimension - Stud Size inch	#4
Dimension - B Length fraction	13/50 in
Dimension - B Length inch	0.26 in
Dimension - Z inch	0.17 in
Dimension - Bolt Size fraction	#4
Cable Insulation Diameter Maximum	0.190 in
Dimension - Length Overall inch	0.77 in
Dimension - Diameter Max Size inch	0.19 in

General

Insulation Type	Vinyl
Trade Name	VINYLUG™
Insulation	Y
Sub Brand	COMPRESSION TERMINAL, VINYLUG
Color Code	Blue
Physical Attribute - Tongue Type	Ring
Plated	Y
Feature - Barrel Style	Shrouded
Type	Ring Tongue
UPC 12 Digit	781810712245
UPC 14 Digit GTIN	00781810712245
Material	Copper
Plating Type	Tin
UPC	781810712245

Logistics

Minimum Pack Quantity	100
Carton Quantity	1200
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand

© 2026 Hubbell Incorporated. All rights reserved
BRDY-TP144-SPEC-EN | REV 4/2026