



Part Number : 1301080083
Product Description : Super-Safeway 15W
Fluorescent Hand Lamp With Handle Ballast
Location and Switch, Cord Type 18/3 SJTW,
Cord Length 15.24m (50.0')
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1005-3



Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights

Series	130108
Description	Super-Safeway 15W Fluorescent Hand Lamp With Handle Ballast Location and Switch, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')
NEMA Configuration	NEMA 5-15
Product Family	Hand Lamps
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678861245

Agency

UL	E59049
----	--------

Electrical

Lamp Wattage - Maximum	15W
Lumens	910
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Cord Type - Primary	18/3 SJTW
Depth	58.40mm (2.300")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A
Lamp Type	F15/T8
Length	411.73mm (16.210")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held

Outlet	None
Packaging Type	Carton

This document was generated on Mar 26, 2024