



Part Number : [731160066](#)
Product Description : MCRF-to-MCRF, 0.81mm Cable Diameter, Length 152.4mm, H18, 50 Ohms, One Piece Per Bag
Series Number : 73116
Status : Active
Product Category : RF Cable Assemblies



Documents & Resources

Drawings
[Drawing 731160066_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF Cable Assemblies
Series	73116
Description	MCRF-to-MCRF, 0.81mm Cable Diameter, Length 152.4mm, H18, 50 Ohms, One Piece Per Bag
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MCRF-to-MCRF
Product Family	RF Connectors, RF Cable Assemblies and RF Components
Product Name	MCRF
Type	RF Cable Assembly
UPC	884982868373

Electrical

Impedance	50Ω
-----------	-----

Physical

Cable Length	152.40m
Circuits (Loaded)	0
Circuits (maximum)	0
Gender	Plug/Plug
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Polyester
Net Weight	0.350/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Coaxial

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
50 Ohms, MCRF, PCB Vertical Jack Receptacle, SMT, 1.25mm Mounted Height	<u>0734120110</u>

This document was generated on Sep 02, 2023