

MPP-ACC-DUST CAP PLUG IP65/67



Image is for illustration purposes only. Please refer to product description.

Part number	09 51 800 0002
Specification	MPP-ACC-DUST CAP PLUG IP65/67
HARTING eCatalogue	https://harting.com/09518000002

Identification

Category	Accessories
Series	HARTING Mini PushPull
Type of accessory	Protection cover
Description of the accessory	for cable side

Version

Locking type	PushPull
--------------	----------

Technical characteristics

Limiting temperature	-40 ... +70 °C
Storage temperature	-60 ... +85 °C
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 / IP67

Material properties

Material (accessories)	Polybutylene terephthalate (PBT)
Colour (accessories)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

Commercial data

Packaging size	1
Net weight	6.4 g
Country of origin	Romania
European customs tariff number	39269097
GTIN	5713140235588
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400