




REV.	DATE	DESCRIPTION
NC	12/01/05	INITIAL RELEASE



NOTE:
1. MAX. BOARD THICKNESS = 1.57mm

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
7						DRAWN	G.R.S.	12/01/05										
6						CHECKED												
5	HEX NUT	BRASS	GOLD	1						PART DESCRIPTION								
4	LOCK WASHER	BRASS	GOLD	1						SMA END LAUNCH RECEPTACLE JACK								
3	CONTACT PIN	BER. COPPER	GOLD	1						PART NO.								
2	INSULATOR	TEFLON	NATURAL	1						132371								
1	BODY	BRASS	GOLD	1						DWG. NO.		132371.DWG	REV.	NC	SIZE	A	SCALE	NA
DESCRIPTION						MATERIAL	FINISH	QTY	CAD FILE		C:/132/132371.DWG							