
1452581-2 Product Details



Active

View 3D PDF

FAKRA II and FAKRA IV RF Connector Systems

1 WAY JACK COAX CONN FAKRA2

1452581-2

TE Internal Number: 1452581-2

Product Highlights View All

- FAKRA II Industry Standard
- Applies To Wire/Cable
- Cable-to-Cable
- Connector - RF
- Housing

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

Documents | Features | Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

Product Type	Connector - RF
Connector Type	Housing

Mechanical Attachment

Mating Retention Type	Latch(ing)

Termination Features

Termination Method to Wire/Cable	Crimp

Dimensions

Length (X-Axis) (mm [in])	26.00 [1.0236]
Width (Z-Axis) (mm [in])	10.90 [0.429]
Profile Height (Y-Axis) (mm [in])	10.30 [0.4055]

Body Features

Mounting Feature	Without
Body Shape	Straight
Mating Retention	With

Contact Features

Contact Type	Socket

Housing Features

Connector Style	Jack
Housing Material	PBT GF10
Housing Color	Signal White
Mating Alignment	With
Mating Alignment Type	Keyed

Configuration Features

Number of Positions	1
Coaxial Cable Type (RG/U or Mfg.)	174, 75 Ohm, RTK 031

Industry Standards

Industry Standard	FAKRA II
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant

Identification Marking

Key Identifier	B

Conditions for Usage

Applies To	Wire/Cable

Operation/Application

Application Use	Cable-to-Cable
Industry Application	Automotive

Other

Industry	Automotive
Brand	AMP

Related Products

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling

© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

Downloaded from Arrow.com.