



LOC	DIST	P	F	ZONE		LTR	DESCRIPTION	DATE	APPD
G	86					D	REV PER 063A-0561-01	030CT02	JR MS



- 1 TIN PL 0.00381 [0.000150] MIN THK PER ASTM B-545
- 2 CRIMP DIES: USE P/N 46756-2 (600 MCM)

55831

B

A

55831-2
PART NO

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON :
2 PLC DEC ± 0.51 [0.020]
3 PLC DEC ± -
ANGLES ± -

MATERIAL

COPPER PER ASTM B-75
ANNEALED

DR 2/6/92
DK SCHRUM

CHK 2/7/92
AJ KAUFMAN

APPD 2/7/92
WJ VOCKROTH

APPD 2/7/92
CR RHODS

PRODUCT SPEC
-

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME

TERMINAL, CENTER LINE
TONGUE, AMPPOWER™
WIRE SIZE: 500 HD MCM

FINISH



APPLICATION SPEC

-

WEIGHT 279 GRAMS

SIZE



CAGE CODE

00779

DRAWING NO

55831

SCALE

1:1

SHEET

1 OF 1

METRIC